


SM-15R/L

Stereotaxic Manipulator

Manipulator with excellent versatility

A coarse movement unit with a long working range is attached to X- and Z-axis respectively. The latter also has fine movement unit attached, which is most important. The fine movement knob positioned at a height with ease of use permits isolation from vibrations in operation. Rotation mechanisms are employed for the vertical and horizontal directions, enabling easy approach from any required tilting angle. The dedicated electrode holder can be replaced for an injector using its attachment.



Accessories included		Dedicated Electrode Holder (for both ø0.5mm and ø1mm) Hex Wrench
Movement range	Coarse	X60mm, Z50mm
	Fine	Z8mm Full rotation of knob 500µm Minimum graduation 10µm
Dimensions/Weight		W120 × D75 × H180mm, 1.25kg

