





The new LN Multipatch System with 3D lock function



The new design of our LNprism, which manufactured in one piece! offers a better prism stability. Together with double of the thickness, this new version of our prism offers the ability to exchange electrodes with zero vibrations.




Our LNscope with inbuilt XY shifting table offers more stability and is resistant to vibrations, thanks to our new low-profile design.



SM10 remote^{touch} includes a unique feature which allows locking each of the manipulators individually to the microscope movement without using a PC connection! Everything is calculated in real time.

We are proud to present our novel flexible patch angle mechanism, that helps to set the angles for the 3D log. Now you can use our LNPrism to manipulate the adjusted angle and to set the angle value in our SM10 remote^{touch}. The rotational angle and the patch angle can be set easily. Together with guided calibration routine, you can increase the accuracy if needed.



The small Footprint of the LN Multi patch unit allows up to 12 LN Units around our LNscope.

LN-Youtube



Follow us on:



YouTube



luigs_neumann