



Inverted trinocular LED fluorescence microscope, IOS U-PLAN F objectives

Observation Method - Transmitted Light	Brightfield	Yes
	Phase contrast (Positive type)	As optional
Observation Method - Incident Light	Fluorescence	Yes
Main Body	Type	Inverted
	Construction material	Aluminum die-cast
Head	Type	Trinocular (Siedentopf)
	Split ratio	100/0 - 50/50
	Inclination	45°
	Interpupillary distance (mm)	50-75
	Dioptric adjustment	On left tube
	Tube inner diameter (mm)	30
Eyepieces	Field number (mm)	22
	Magnification	10x
	Planar type	Yes
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	26
	High eyepoint (for glass wearers)	Yes
	Rubber cup	Yes
	Retractable protections	Yes
Nosepiece	Positions	Quintuple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
Objectives	Optical system	∞
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	100x-400x
	Type	IOS LWD U-PLAN F
		IOS LWD U-PLAN F 10x/0.30, W.D. 7.11 mm
		IOS LWD U-PLAN F 20x/0.45, W.D. 5.91 mm
	IOS LWD U-PLAN F 40x/0.65, W.D. 1.61 mm	

Stage	Type	Fixed + Attachable mechanical stage
	Dimensions (mm)	250x160 (fixed stage) 250x290 (with mechanical stage mounted)
	Moving mechanism	Rack and pinion
	Moving range (mm)	120x80
	Material	Anti-scratch painting
	Glass round insert	Included
	Metal round insert	Included
	Holder for Petri dish (mm)	54 (Included); 38, 65 (As optional)
	Holder for Terasaki plate	96 well (Included)
	Holder for 1 slide	Included
	Holder for 2 slides	As optional
Holder for Utermöhl chamber	As optional	
Condenser - Single Position	Type	Abbe
	Removable	Yes
	Numerical aperture (N.A.)	0.30
	Diaphragms	Iris
	Long working distance	Yes
	Working distance (for LWD) (mm)	72
	Extendable working distance (for LWD) (mm)	up to 150
Focusing System	Type	Coaxial coarse & fine
	Fine total travel (per single rotation) (mm)	0.2
	Fine graduations	100
	Fine resolution (µm)	2
	Upper stop to prevent contact	Yes
	Adjustable tension	Yes
Transmitted Illumination	Type	X-LED
	X-LED type	X-LED8
	Light source power (W)	8
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	13
Power Supply	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	12 Vdc 7 A
Accessories Included	Dust cover	Yes
	Allen wrench	Yes
	User Manual	Digital version (downloadable)
Additional Information		Metallic interchangeable inserts for slides, Petri dishes, Terasaki, multi-Well plates (as optional).
Product Dimensions	Height (mm)	495
	Width (mm)	365
	Depth (mm)	540
Product Weight	(kg)	12

Fluorescence Attachment	Number of LED Cubes	Up to 4
	BLUE LED Cube (Optional)	LED Emission: 460 nm. Excitation: 455 - 495 nm; Dichroic: 500 nm; Emission: 510LP nm
	BLUE BANDPASS LED Cube (Optional)	LED Emission: 460 nm. Excitation: 455 - 495 nm; Dichroic: 500 nm; Emission: 518-542 nm
	GREEN LED Cube (Optional)	LED Emission: 523 nm. Excitation: 510 - 550 nm; Dichroic: 570 nm; Emission: 575LP nm
	GREEN BANDPASS LED Cube (Optional)	LED Emission: 523 nm. Excitation: 510 - 550 nm; Dichroic: 570 nm; Emission: 585-625 nm
	UV LED Cube (Optional)	LED Emission: 365 nm. Excitation: 325 - 375 nm; Dichroic: 415 nm; Emission: 435LP nm
	UV BANDPASS LED Cube (Optional)	LED Emission: 365 nm. Excitation: 340 - 390 nm; Dichroic: 405 nm; Emission: 420-470 nm
	V LED Cube (Optional)	LED Emission: 405 nm. Excitation: 390 - 420 nm; Dichroic: 440 nm; Emission: 450LP nm
	RED1 LED Cube (Optional)	LED Emission: 623 nm. Excitation: 590 - 650 nm; Dichroic: 660 nm; Emission: 665LP nm
	RED2 LED Cube (Optional)	LED Emission: 623 nm. Excitation: 595 - 645 nm; Dichroic: 655 nm; Emission: 665-715 nm
	DEEP RED LED Cube (Optional)	LED Emission: 660 nm. Excitation: 623 - 678 nm; Dichroic: 685 nm; Emission: 690-750 nm
	FAR RED LED Cube (Optional)	LED Emission: 740 nm. Excitation: 720 - 760 nm; Dichroic: 770 nm; Emission: 780LP nm
	AMBER LED Cube (Optional)	LED Emission: 590 nm. Excitation: 582 - 603 nm; Dichroic: 610 nm; Emission: 615-645 nm
	<i>Contact OPTIKA for other custom LED Fluorescence Cube options</i>	
Filter set selection	Manual	
LED source insertion	Manual	

Fluorescence Light Source	Light source	LED Fluorescence Cube
	Light source power (W)	3.5
	LED wavelength	<i>see LED Fluorescence Cube specs</i>
	Lifetime (hours)	> 65,000
	Brightness control	Yes